

Screwless Terminated InsulGrip[®] Flanged Receptacle**Features**

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

Ordering Information

| Description | UPC | Catalog Number |
|--------------------------|-------------|------------------|
| Nylon casing, back wired | 78358571924 | HBL2826ST |

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

| | |
|-----------------------|-----------------------|
| Housing | Nylon |
| Terminal Retainer | Nylon |
| Plunger | Nylon |
| Contacts | Brass |
| Terminal Spring Clamp | Spring Steel |
| Assembly Screws | Zinc Plated Tri-drive |
| Weight (lbs) | 0.4 |

Performance**Electrical**

| | |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 3,000V minimum |

Mechanical

| | |
|-------------------------|--|
| Terminal Accommodation | #14 AWG - #10 AWG solid or #14 AWG - #8 AWG stranded copper wire |
| Terminal Identification | Terminals identified in accordance with UL 508 |

Environmental

| | |
|------------------------|---|
| Flammability | HB or better per UL94/CSA 22.2 No.0.17 |
| Moisture Resistance | IP20 Suitability |
| Operating Temperatures | Maximum Continuous 75°C, Minimum -40°C (w/o impact) |

**Online Resources**

Customer Sales Drawings
eCatalog
Installation Instructions