

Twist-Lock<sup>®</sup> EdgeConnect<sup>™</sup>

15A 125V,2-Pole 3-Wire Grounding, L5-15R

Panel Mount Receptacle



Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.

Ordering Information

Description	Device Color	UPC	Catalog Number
Single, Panel Mount, Black	Black	783585719665	HBL4713ST

Listings

Listed to UL 498  
Fed.Spec. W-C-596  
Certified to CSA C22.2 No.42

Specifications

Face	Polycarbonate
Base	Polycarbonate
Plunger	Nylon
Contacts	Brass
Terminal Spring Clamp	Spring Steel

Performance

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
<b>Mechanical</b>	
Terminal Accommodation	#14 AWG - #10 AWG stranded copper wire only
Terminal Identification	Terminals identified in accordance with UL 498
<b>Environmental</b>	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C, Minimum -40°C (w/o impact)



Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

