Surge Protective Devices

20A 125V, 5-20R

SpikeShield[®] Specification Grade Isolated Ground Duplex Receptacle

Features

- IG triangle on the face of the receptacle clearly indicates isolated ground device on the face of the receptacle
- A "Clean" Path Provides A "Clean" Ground For Sensitive Equipment
- · Power-on indicator light

Ordering Information

DescriptionColorIsolated ground, surge
suppression duplex
receptacles with light and
alarm, 240 joules/15000A
per mode.Blue

UPC 783585060873

Catalog Number 0873 IG5362SA


Listings

CSA Certified to Specification C22.2 No. 42 Listed to UL Standards 498 UL Listed File E2186

Specifications

Application Environmental Conditions

Indicator(s) Type Item Type Material Outlet Connectivity Frequency Rating Phase Decorator Duplex with Light and Alarm Indoor Dry Unless Protected By Additional Means LED and Audible Alarm Surge Protection Receptacles Composite Straight Blade Terminal Screws 60 Hz Single Phase



Performance

Electrical Protection Modes Response Time Transient Suppression

Voltage

Environmental Flammability Operating Temperature Normal and Common Modes Approximately 5 ns Peak Energy (10 X 100 µs), Peak Current (8 X 20 µs) 120V AC + 10% - 15%

UL 94V-2 32°F to 140°F (0°C to 60°C)

Online Resources

Customer Sales Drawings eCatalog Installation Instructions



