

Linkosity Products

Female Receptacle

Female Receptacle, 20A Single, 5'



Ordering Information

Color	UPC	Catalog Number
Gray	783585116259	RF2303PB005

Specifications

Special Features	Super Neutral and IG, Green/Yellow/White/Black Wires
Application	Power and Control Integration
Voltage Rating	600V Max kV
Current / Amperage Rating	20 A
Conductor Size	#12 AWG, #10 AWG Neutral
Number of Poles	5-Pole



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

