

Linkosity Products

Female Receptacle

Female Receptacle, 30A 4W



Ordering Information

Color	UPC	Catalog Number
Gray	783585504650	RF3004PB001

Specifications

Special Features	Green/Yellow/White/Black Wires
Application	Power and Control Integration
Voltage Rating	600V Max kV
Current / Amperage Rating	30 A
Conductor Size	#10 AWG
Number of Poles	4-Pole



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

