

TradeSelect

15 A, 125 VAC, 2-Pole, 3-Wire Grounding

## Duplex Receptacle, Residential Grade, Weather Resistant/Tamper Resistant

### Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

### Ordering Information

Color	UPC	Catalog Number
Gray	883778303906	RR15SGYWRTR

### Specifications

NEMA Rating	5-15R
Wire Size	#14 AWG to #12 AWG
Wattage	1875
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Special Features	Weather Resistant and Tamper Resistant
Phase	Single Phase

# HUBBELL



### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

