TradeSelect

15 A, 125 VAC, 2-Pole, 3-Wire Grounding

Residential Grade, Receptacles, Tamper Resistant Duplex

HUBBELL

Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Ordering Information

 Color
 UPC
 Catalog Number

 Ivory
 883778301520
 RR15SITR

Specifications

NEMA Rating 5-15R

Wire Size #14 AWG to #12 AWG

Wattage 187

Environmental Conditions Indoor Dry Unless Protected By Additional

∕leans

Special Features Tamper Resistant- Self Grounding

Phase Single Phase

Performance

Environmental

Operating temperature 20°C to 60°C


Mechanical

Terminal Terminal screws accepts up to #12 AWG, Push

wire designed for #14 AWG solid copper wire

only





Online Resources

Customer Sales Drawings eCatalog

