#### **TradeSelect**

# 20 A, 125 VAC, 2-Pole, 3-Wire Grounding

# Residential Grade, Receptacles, Single

## Features

- · Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- · Tough thermoplastic ultrasonically welded cover and base

### **Ordering Information**

 Color
 UPC
 Catalog Number

 Brown
 883778100253
 RR201

### **Specifications**

NEMA Rating 5-20R

Wire Size #12 AWG to #10 AWG

Wattage 250

Environmental Conditions Indoor Dry Unless Protected By Additional

Means

Special Features Self Grounding
Phase Single Phase

### **Performance**

20°C to 60°C

Terminal Terminal screws accepts up to #12 AWG, Push

wire designed for #14 AWG solid copper wire


only

**Environmental** 

Operating temperature







#### **Online Resources**

Customer Sales Drawings eCatalog Installation Instructions

