

## Ground Fault Products

### Commercial Hospital Grade Tamper-Resistant and Weather Resistant GFCI Receptacles

# HUBBELL

#### Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Green power indicator and red trip indicator

#### Ordering Information

Description	Color	UPC	Catalog Number
15A, 125V, Style Line®, hospital grade, SNAPConnect®, AUTOGUARD® self test GFCI receptacle, tamper-resistant and weather resistant	Red	783585746258	SNAPGFTW82R

#### Listings

UL Listed - Canadian and U.S.  
Meets ADA Standards  
Meets all NEC® requirements  
CSA Certified  
NEMA® WD-6 Compliant

#### Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Brass
Mounting Screws	Stainless steel

#### Performance

##### Electrical

Amperage	15A/20A, 20A Feed Thru
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Frequency	60 Hz
Maximum Interrupting Capacity	10,000A
Trip Level	4 to 6 mA
Trip Time	.025 second nominal
Voltage	120V AC +10% - 15% (102V to 132V)

##### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

##### Environmental

Flammability	UL 94V-0
Operating Temperature	-35°C to 66°C or -30°F to 150°F

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484  
Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



#### Related Products

Wallplates for duplex openings      Solid Right Angle Pigtailed Terminal

SNAP1RA      Stranded Right Angle Pigtailed Terminal

SNAP2RA

#### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

