

Yoke Plate, Triangular

by ANDERSON
Catalog ID: YPD30152382

Yoke Plate, Delta, Ductile Iron, UTS 30,000 lb



* Representative image

Product Details

General

Material	Ductile Iron
Number of Bolt Holes	0
Series	YPD Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
Type	Suspension Tangent Yokes
UPC	096359344841

Dimensions

Assembly Rating (Ultimate)	0 lb
Base Hole Spacing	9 in
Diameter - Apex Hole	1.25 in
Diameter - Base Holes	1.25 in
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	9 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	6 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness at Apex	0.75 in
Thickness at Base	0.75 in

Weight	7.350 lb
--------	----------

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com