



Yoke Plate, Rectangular

by ANDERSON
Catalog ID: YPR6019401

Yoke Plate, Rectangular, Ductile Iron, UTS 60,000 lb



* Representative image

Product Details

General

Corona Ring Mounting Provision	4 x 0.500" -13 UNC Tapped holes
Material	Ductile Iron
Number of Bolt Holes	0
Series	YPR Series
Strength Rating - Ultimate	60000 lb
Strength Rating - Ultimate Body	0 lb
Type	Strain Yokes
UPC	096359345312

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator Attachment Holes	0.938 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	6 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.75 in
Weight	24.500 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in
Diameter - Conductor Attachment Holes	0.938 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: hpsintlcs@hubbell.com