

ZQU6-350SLR

by CMC

Catalog ID: ZQU6-350SLR



Space-saver stud-mount transformer connectors, slip fit, Dual rated connectors for Aluminum or Copper conductors, Right-hand mounting, Right-hand mounting, CO-OX Oxide inhibitor is omitted

- Fully tested to ANSI C119.4 for Class "A" connectors.
- Supplied with aluminum radial-tipped set-screws.
- 105°C Rated clear plastisol cover available.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes CO-OX oxide inhibitor in all conductor holes and stud mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.
- A torque wrench should be used to ensure the proper torque is achieved.

Product Details

General

Material	Aluminum Alloy, 6061-T6
UPC	192663085361

Dimensions

Height	2.88 in
Length	5.13 in
Width	2.38 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
-----------------	---------------------



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

