



ZS6-350BSLI

by CMC

Catalog ID: ZS6-350BSLI

Space-saver stud-mount transformer connectors, screw on, Dual rated connectors for Aluminum or Copper conductors, Street light tap is available

- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of an insulated Allen wrench.
- A torque wrench should be used to ensure the proper torque is achieved.
- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Supplied with aluminum radial-tipped set screws.
- 105°C Rated clear plastisol cover available.

Product Details

General

Material	Aluminum Alloy, 6061-T6
UPC	192663086924

Dimensions

Height	2.38 in
Length	4.25 in
Width	2 in

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
Number Of Conductors	6