



ZS8-500ASLI

by CMC

Catalog ID: ZS8-500ASLI

Space-saver stud-mount transformer connectors, Dual-Rated for Aluminum or Copper Conductors

- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole
- Each unit individually wrapped and labeled ease of identification and cleanliness
- For installation, CMC® recommends the use of an insulated Allen wrench
- A torque wrnch should be used to ensure the proper torque is achieved
- Clear plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Supplied with aluminum radial-tipped set screws
- 105°C Rated clear plastisol cover available
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength

Product Details

General

Series	ZLC
Type	ZS

Dimensions

Dimensions	6.25 in x 2.38 in x 2.88 in
Height	2.88 in
Length	6.25 in
Width	2.38 in

Conductor Related

Conductor Range	500 Kcmil - #10 AWG
Number Of Conductors	8



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

