

ZS8-500SLCI

by CMC
Catalog ID: ZS8-500SLCI



Space-saver stud-mount transformer connectors

- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole
- Each unit individually wrapped and labeled ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.
- Clear plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Supplied with aluminum radial-tipped set screws
- 105°C Rated clear plastisol slip-on cover
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength

Product Details

Dimensions

Height	3.5 in
Length	7.25 in
Width	3 in

Conductor Related

Conductor Range	500 Kcmil - #10 AWG
-----------------	---------------------