

ZSU8-500SLCI

by CMC

Catalog ID: ZSU8-500SLCI



Space-saver stud-mount transformer connectors, screw-on, Dual rated connectors for Aluminum or Copper conductors

- Clear plated for low-contact resistance.
- Fully tested to ANSI 119.4 for Class 'A' Connectors.
- Supplied with aluminum radial-tipped set screw.
- 105 C Rated clear plastisol slip-on cover.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.

Product Details

General

Material	Aluminum Alloy, 6061-T6
UPC	192663076925

Dimensions

Height	3.5 in
Length	7.75 in
Width	3.25 in

Conductor Related

Conductor Range	500 Kcmil - #10 AWG
Number Of Conductors	8