

### **FEATURES**

- Available 2', 3', 4', or 8'
- · Heavy die formed steel channel
- Snap-on cover. No tools required. No hardware to lose
- · Rotary lock lampholders for positive lamp contact
- · Channel ends double as joiners
- Individual or row mounting. Surface or suspended

| PROJECT INFORMATION |      |
|---------------------|------|
| Project Name        | Туре |
| Catalog No          |      |

#### **CONSTRUCTION**

Heavy gauge cold rolled steel housings fully assembled. Channel cover provides room-side access to ballast.

#### **FINISH**

White painted parts are treated with a five stage phosphate bonding process and finished with a high reflectance baked enamel.

### **BALLASTS**

Energy efficient, thermally protected, automatic resetting, Class P, high power factor, sound rated A, unless otherwise specified. CEE NEMA Premium compliant.

## **ELECTRICAL**

Standard class "P", thermally protected, autoresetting HPF ballast, sound rated A. CEE NEMA Premium compliant. All ballast leads extend a minimum of 6" through access location. NEC/CECcompliant ballast disconnect is standard.

## CERTIFICATION

All luminaires are built to UL 1598 standards and bear appropriate UL and cUL or CSA labels. Damp location labeling is standard. Emergency-equipped fixtures labeled UL 924.

# **ORDERING INFORMATION**

**EXAMPLE CH4-132-E347-GLR** 

| СН                  |                      |                                      |  | - <u>E</u>                                     |                     |  |
|---------------------|----------------------|--------------------------------------|--|--|---------------------|--|
| MODEL CH Heavy Duty | <b>SIZE 2</b> '      | NO. OF LAMPS IN<br>CROSS SECTION     | <b>LAMP TYPE 17</b> 2', T8: 17 Watt                            | BALLAST  E Electronic T8, Instant Start        | VOLTAGE U 120V-277V | OPTIONS GLR Fast Blow Fuse   |
| Narrow Channel      | 3 3'<br>4 4'<br>8 8' | <ol> <li>One</li> <li>Two</li> </ol> | 25 3', T8: 25 Watt<br>32 4', T8: 32 Watt<br>21 3', T5: 21 Watt | For a specific ballast vendor, show as option. | <b>347</b> 347V     | GMF Slow Blow Fuse EL Emergency Battery Pack PAF Paint After Fabrication |
|                     |                      |                                      | 28 4', T5: 28 Watt<br>54 4', T5HO: 54<br>or 51 Watt            |  | I                   | ACCESSORIES<br>(ORDER SEPARATELY)  |

on a T-Bar ceiling

CHWG3 3' Wire Guard

**CHWG4** 4' Wire Guard, 2 required for 8' fixture

CHRA3 3' Asymmetric Reflector<sup>1</sup>

CHRA4 4' Asymmetric Reflector, 2 required for 8' fixture1

CHR3 3' Symmetric Reflector<sup>1</sup>

CHR4 4' Symmetric Reflector, 2 required for 8' fixture1

Reflectors fit 1-lamp profiles only. Page 1/2 Rev. 12/11/17


© 2017 Columbia Lighting, a division of Hubbell Lighting, Inc. Specifications subject to change without notice.




STRIPLIGHTS / CH




### **DIMENSIONAL DATA**



### **MOUNTING DATA**



### **ACCESSORY REFLECTORS FOR ONE LAMP PROFILE**



NOTE: All dimensions are in inches; dimensions and specifications are subject to change without notice. Please consult factory or check sample for verification.

HUBBELL Hubball Highting Inc