



Catalog Number	
Comments	Type

FEATURES

Application

The CCU2 Series offers emergency lighting for commercial applications. The housing is made of durable 20-gauge steel providing strength and durability. AC power on LED indicator with push-to-test switch. Meets City of Chicago code requirements.

Construction

The housing is made of heavy-duty 20 gauge steel in white finish. The two 5.3W Lamp heads in white finish are adjustable.

Installation

Knockouts are located on the back for wall mounting. Side and top knockouts for conduit feed applications.

Illumination

Two 6V, 5.3W Lamp heads standard. Remote capacity option for 20W models. Will run two LED CRH heads ordered separately.

Compliances

Listed to UL924 Standard
 City of Chicago Fire Code Approved
 Damp Location Listed (20°C to 50°C)
 NFPA 101
 NEC
 OSHA

Warranty

Full 5 year warranty



ORDERING GUIDE

CCU2



Blank - 10W
RC - Remote Capacity (20W)

ACCESSORIES

CRHO - Outdoor Remote for Chicago
CRHI - Indoor Remote for Chicago



Outdoor Remote Head

Indoor Remote Head



SPECIFICATIONS

Electronics

100% solid state switching includes low voltage disconnect to prevent full battery dis-charge and AC lock-out feature. Emergency model includes maintenance-free sealed lead acid battery with capacity to run the LED's for 90 minutes. 24 hour battery re-charge. All models supplied with a dual voltage input which accepts 120 or 277VAC. Includes pre-stripped AC pigtail leads. Includes test switch and AC-on indicator.

Battery Type: Sealed Lead Acid

Input: Dual 120/277 voltage

Operating Temperature Range : 20°C to 50°C

Weight: CCU2: 6.7

CCU2RC: 8.2

MAXIMUM POWER CONSUMPTION

CATALOG NUMBER	INPUT WATTS (W)		INPUT AMPS (A)	
	120V	277V	120V	277V
CCU2	8.4	9.4	0.08A	0.04A
CCU2RC	8.7	10.0	0.09A	0.05A

DIMENSIONS

