

APPLICATIONS

Suitable for fire-rated ceiling assemblies in new construction where insulation is not present or is spaced 3" away. The FT4 is ideal for applications that require a small, concealed source to maintain a clean ceiling plane. Specify the FT4 to accent items of interest in retail spaces, hospitality environments, residentially in bedrooms, living rooms, foyers, and hallways, or to supplement the general illumination in commercial and multifamily projects.

REFLECTOR

Trims feature three simple spring retention clips to ensure a snug fit to the ceiling plane, eliminating unwanted light leaks and sagging over time. All trims are made of high quality stamped steel and have an integral trim flange. Reflectors are anodized to reduce the risk of yellowing, cracking or warping. Matte white trim ring standard.

LAMP/SOCKET

CATALOG NUMBER:

Socket snaps into trim carrier to place lamp in proper position ensuring consistent appearance and performance. Porcelain socket with brass or copper screwshell. Thermal protector prevents fixture from overheating when improperly installed or over-lamped. Refer to trim for specific lamp information. Lamps furnished by others.

New Construction **FT4**

Bar hangers with integral T-bar mounting clips and nail tab for wood joist construc-

tion. Accommodates up to 24" on center

ceiling joists. Captive bar hangers will lock

to secure housing in place. For unstallation

of bar hangers to furring channels, order

Steel housing adjusts vertically to accom-

modate ceilings up to $2\frac{1}{2}$ " thick. Two (2)

splices. Integral Romex clamp. Six pieces of UL classified fire resistant gypsum board

attached to housing. Fiberglass gasket on

bottom of frame to minimize heat transfer

Prewired steel junction box with prein-

stalled ground wire. Housing may be re-

Non-IC rated. Insulation, if present, must

be spaced 3" away from housing. UL and

CUL listed for damp locations and through

wiring. Thermally protected. UL classified

to maintain up to a one hour fire rating in

ceiling assemblies. UL classified to maintain fire ratings up to 2 hours in all UL D200, G200, L200, D500, G500, and L500 series fire rated floor/ceiling

UL P200 and P500 series fire rated roof

moved from plaster frame after installation

snap-on covers provide easy access to

FTFCC furring channel clips.

HOUSING

into ceiling cavity.

to provide access to J-box.

J-BOX

LABELS

assemblies.

INSTALLATION

4" Fire Resistant Recessed Line Voltage Incandescent Downlight One PAR-16 or PAR20/R20 Lamp Non-IC Rated 120V

DATE:		

FIRM NAME:


PROJECT:


🚸] FireTight

4"

Aperture: Nominal 4" Ceiling Cutout: 4½" Maximum Ceiling Thickness: 2½" For conversion to millimeters, multiply inches by 25.4 Weight: 14 lbs. Not to Scale

TYPF





US Patent No. 6,357,891; 6,004,011

EXAMPLE: FT4-TA120C

HOUSING	TRIMS	TRIMS	TRIMS	ACCESSORIES
□ FT4	ADJUSTABLE TA 1 20(C) TA 1 20E	ADJUSTABLE BAFFLE TA120BF TA120WBF	ADJUSTABLE WALL WASH	 FTFCC 4 clips to install bar hangers to furring channels ICBOX Recessed enclosure
				for IC applications Refer to specificati sheet FT-INC-005



In a continuing effort to offer the best product possible we reserve the right to change, without notice, specifications or materials that in our opinion will not alter the function of the product. Web: **www.prescolite.com** • Tech Support: **(888) 777-4832**

TRIMS & FINISHES

Adjustable



TA120C Specular clear anodized reflector with 360°H x 20°V adjustment. Max. 45W PAR16, 50W PAR20/R20



TA 1 20E Eyeball, white interior with 360°H x 20°V adjustment. Max. 75W PAR16, 50W PAR20

Adjustable Baffle



TA120BF Black spun baffle with 360°H x 20°V adjustment. Max. 45W PAR16, 50W PAR20/R20



TA120WBF White spun baffle with 360°H x 20°V adjustment. Max. 45W PAR16, 50W PAR20/R20

Adjustable Wall Wash



TA120WW Wall washer with spun black baffle with 360°H x 20°V adjustment. Max. 30W R20

Refer to <u>www.prescolite.com</u> for photometrics.



Web: www.prescolite.com • Tech Support: (888) 777-4832 701 Millennium Blvd., Greenville, SC 29607 U.S.A. • Phone (864) 678-1000 Copyright ©2013 Prescolite, Inc., a division of Hubbell Lighting, Inc. All Rights Reserved Specifications subject to change without notice. • Printed in U.S.A. • FT-CFL001 • 6/5/13

