



6" Direct Ceiling Mount Cylinder

1145

One 100W A19 or 150W A21 Lamp
120V

DATE: _____ TYPE: _____

FIRM NAME: _____

PROJECT: _____

LiteForms™

For conversion to millimeters,
multiply inches by 25.4
Not to Scale

APPLICATIONS:

The 1145 is a 6" ceiling mounted cylinder that is properly scaled for use with A19 or A21 lamp sources. The 1145 is suitable for a wide variety of commercial, retail and institutional applications.

HOUSING:

.058" thick seamless extruded aluminum cylinder with durable powder coat paint finish. 16 gauge C.R.S. socket/reflector mounting bracket. Specify: brushed aluminum, matte black, bronze, matte white or Prescolite's exclusive Zet, metallic silver.

REFLECTOR:

High purity aluminum Alzak reflector available in specular clear or champagne gold Alzak. Optical system provides excellent glare and brightness control for visual comfort.

LAMP:

One (1) 100W A19 or 150W A21 lamp.
Lamps furnished by others.

SOCKET:


Two position porcelain socket with nickel plated screw shell.

INSTALLATION:

Easy installation onto standard J-Box.

LABELS:

UL, CSA listed for damp locations



CATALOG NUMBER:

EXAMPLE: 1145-363BZ

HOUSING

FINISH OPTIONS

☐ 1145-362

6" Ceiling mount cylinder with clear Alzak reflector.
One 100W A19 or 150W A21

☐ 1145-363

6" Ceiling mount cylinder with champagne gold Alzak reflector.
One 100W A19 or 150W A21

☐ BA

Brushed aluminum

☐ BL

Matte black

☐ BZ

Bronze

☐ WH

Matte White

☐ Z

"Zet" metallic silver

PHOTOMETRIC DATA

LiteForms™ - 6" Direct Ceiling Mount Cylinder - 1145

NOTES

Refer to www.prescolite.com for additional photometric tests (IES Files).



Web: www.prescolite.com • Tech Support: (888) 777-4832
701 Millennium Blvd., • Greenville, SC 29607 U.S.A. • Phone (864) 678-1000
Copyright ©2010 Prescolite, Inc., a division of Hubbell Lighting, Inc. All Rights Reserved
Specifications subject to change without notice. • Printed in U.S.A. • LFO-INC-010 • 1/19/10



Hubbell Lighting, Inc.