

WGL

**Approvals** 

PRODUCT IMAGE(S)

**DIMENSIONS** 

## **INTENDED USE**

• Designed for perimeter illumination of walls with typical mounting heights of 15'-25'

## **CONSTRUCTION**

- Die-cast aluminum housing and door, provides rigid mounting to wall; dissapates fixture heat for long component life and protection from the elements
- Aluminum reflector designed to provide a uniform full cut-off, neighbor friendly Type II distribution for wide lateral spacing
- Castings are powder painted dark bronze for and lasting protection
- Clear tempered glass lens thermal shock and impact resistant

## **ELECTRICAL**

• HID ballasts are HPF, multi-tap (120, 208, 240, 277V)

### INSTALLATION

• 1/2" conduit hubs located on top and sides of the back of housing

### **LISTINGS**

· Listed to UL1598 for use in wet locations

# A B C

17.2

(438 mm)

18.0

(456 mm)

9.84

(250 mm)

## **CERTIFICATIONS/LISTINGS**







# ORDERING INFORMATION

| Catalog Number   | Wattage/Source | Voltage             | Finish | Input amps – 120-277V | Lamp | Weight<br>lbs. (kg) |  |
|------------------|----------------|---------------------|--------|-----------------------|------|---------------------|--|
| WGL – Mogul Base |                |                     |        |                       |      |                     |  |
| WGL-250S         | 250w HPS       | 120, 208, 240, 277V | Bronze | 2.6 - 1.2             | ED18 | 32 (14.5)           |  |
| WGL-400S         | 400w HPS       | 120, 208, 240, 277V | Bronze | 4.0 - 1.7             | ED18 | 32 (14.5)           |  |

### **ACCESSORIES - ORDER SEPARATELY**

| Catalog Number | Description                               |  |  |
|----------------|---|--|--|
| PBT-1          | Photocontrol, button type, 120V           |  |  |
| PBT-234        | Photocontrol, button type, 208, 240, 277V |  |  |

# REPLACEMENT PARTS

| Catalog Number | Description              |  |  |
|----------------|--------------------------|--|--|
| SM313GLASS     | Replacement lens for WGL |  |  |

