



## BD24N Flexible Copper Braid, 24 in L, Flexible copper braid jumpers designed to take up linear expansion and contraction

By Burndy  
Catalog # [BD24N](#)

Flexible Copper Braid, 24 in L, Flexible copper braid jumpers designed to take up linear expansion and contraction



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### Application

Flexible copper braid jumpers designed to take up linear expansion and contraction

### Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

### Configuration

Connector Type	Braid
----------------	-------

### Current

Rating - Indoor Amperage	190 A
--------------------------	-------

Rating - Outdoor Amperage	225 A
---------------------------	-------

### Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	610 mm
Dimension - Pad Width inch	0.94 in
Package Height	0.000 in
Dimension - Hole Size inch	0.56 in
Width	0.94 in
Length	24 in
Dimension - Length Overall inch	24.00 in
Dimension - D inch	3.00 in
Height	0.13 in
Dimension - N inch	0.62 in
Dimensions	24 in x 0.94 in x 0.13 in

### General

Material - Ferrules	Y
Sub Brand	BRAID JUMPER
Physical Attribute - Number of Braids	1
Plated	Y
Type	B, Flexible
UPC 12 Digit	781810807231
UPC 14 Digit GTIN	00781810807231
Material	Copper
Plating Type	Tin
UPC	781810807231

### Logistics

Carton Quantity	25
Pallet Quantity	1500

### Product Assets

[Catalog \[English\]](#)