

Industrial Grade, Motor Disconnect
Switch, Unfused, 3 Pole, 30A 600V
AC, Screw Terminals, IP69k, NEMA
Type 4X, 12 Non-Metallic Sloped
Top Enclosure

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS30](#)



Industrial Grade, Motor Disconnect Switch, Unfused, 3 Pole, 30A 600V AC, Screw Terminals, IP69k, NEMA Type 4X, 12 Non-Metallic Sloped Top Enclosure, cULus, NSF, CE, UL 508 / UL 60947-4-1A

Application

Heavy Duty Industrial and/or Washdown

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage
- Electrical - Dielectric Voltage - Withstands 3000V AC minimum
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V0 Classification
- Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

Catalog Number	HBLDS30
Color	Gray
Enclosure Type	IP69k and UL Type 4X, 12
Environmental Conditions	Indoor and Outdoor
Horsepower - Maximum	15
Ingress Protection	IP69k and UL NEMA Type 4X, 12
Material - Mounting Hardware	Stainless Steel Screw Mounting
Mounting Method	External fully adjustable feet
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C

Series
Specifications

- Non-Fused
- Base - Valox®
 - Enclosure Gasket - Neoprene
 - Handle - Valox®
 - Shaft (Unfused) - Valox®
 - Top - Valox®
- Heavy Duty
Disconnect Switches
783585763002

Style
Type
UPC

Dimensions

Height	4.12 in
Hub Size	3/4"
Weight	2.6 lb

Electrical Ratings

Current / Amperage Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

Conductor Related

Wire Size	#14 AWG to #8AWG
-----------	------------------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
Industry Standard(s)	cULus Listed

Product Assets

[Brochures - Circuit-Lock® Motor Disconnects](#)
[Catalog Page - WDK F-5 Catalog Page](#)
[Installation Manuals - HUBBELL 30 AMP CIRCUIT-LOCK DISCONNECT SWITCH | Installation manual](#)
[Literature - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)

