

## Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic Sloped Version Replacement Cover for 30A - HBLDS30 and HBLDS30T Series

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS30RC](#)

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic  
Replacement Cover for 30A Version, HBLDS30 and HBLDS30T  
Series



### Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Truly captive screws prevent lost screws

### Application

Heavy Duty Industrial and/or Washdown

### Specifications

Industry Standard(s)	cULus Listed
Environmental Conditions	Indoor and Outdoor

### Dimensions

Weight	0.9 lb.
--------	---------

### General

Material - Mounting Hardware	Stainless Steel Screw Mounting
Type	Accessories
Enclosure Type	IP69k and UL Type 4X, 12
Series	Non-Fused
Specifications	<ul style="list-style-type: none"><li>• Enclosure Gasket - Neoprene</li><li>• Handle - Valox®</li><li>• Shaft (Unfused) - Valox®</li><li>• Top - Valox®</li></ul>
UPC	783585763132
Ingress Protection	IP69k, NEMA Type 4X, 12
Style	Replacement Cover
Color	Gray

### Logistics

Carton Quantity	10
-----------------	----

### Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C

### Product Assets

<a href="#">Catalog Page [English]</a>
<a href="#">Installation Manual [French, English]</a>