

Industrial Grade, Motor Disconnect,
Unfused Switch, Non-Metallic Sloped
Version Replacement Cover for 60A -
HBLDS60 and HBLDS60T Series

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS60RC](#)

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic
Replacement Cover for 60A Version, HBLDS60 and HBLDS60T
Series

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Truly captive screws prevent lost screws

Application

Heavy Duty Industrial and/or Washdown

Specifications

Industry Standard(s)	cULus Listed
Environmental Conditions	Indoor and Outdoor

Current

Current / Amperage Rating	60 A
---------------------------	------

Dimensions

Weight	1.2 lb.
--------	---------



Height	5.94 in
--------	---------

General

Material - Mounting Hardware Type	Stainless Steel Screw Mounting Accessories
Enclosure Type Series	IP69k and UL Type 4X, 12 Non-Fused
Specifications	• Enclosure Gasket - Neoprene • Handle - Valox® • Shaft (Unfused) - Valox® • Top - Valox®
UPC	783585763293
Ingress Protection Style	IP69k, NEMA Type 4X, 12 Replacement Cover
Color	Gray

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)