

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic Sloped Version Replacement Cover for 60A With Jog - HBLDS60 and HBLDS60T Series

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS60RCJ](#)

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic Sloped Replacement Cover for 60A With Jog, HBLDS60 and HBLDS60T Series

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Factory installed Hold, Off, Auto jog switch for increased safety and point of use communication to PLC
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Factory installed Hold, Off, Auto jog switch for increased safety and point of use communication to PLC

Application

Heavy Duty Industrial and/or Washdown

Specifications

Industry Standard(s) cULus Listed
Environmental Conditions Indoor and Outdoor

Dimensions



Weight

1.2 lb.

General

Material - Mounting Hardware Type
Enclosure Type Series Specifications

Stainless Steel Screw Mounting Accessories
IP69k and UL Type 4X, 12 Non-Fused
• Enclosure Gasket - Neoprene
• Handle - Valox®
• Shaft (Unfused) - Valox®
• Top - Valox®
783585763316
IP69k, NEMA Type 4X, 12 Replacement Cover
Gray

UPC
Ingress Protection Style Color

Operational

Operating Cycles
Operating Temperature

10,000 Cycles Minimum
Without Impact Maximum continuous 75°C and minimum -40 °C

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)