

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic Sloped Version Replacement Cover for 60A With inTOUCH Installation Free LED Phase Indication - HBLDS60 and HBLDS60T Series

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS60RCP](#)

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic Replacement Cover for 60A With inTOUCH Installation Free LED Phase Indication, HBLDS60 and HBLDS60T Series



Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements

Application

Heavy Duty Industrial and/or Washdown

Specifications

Industry Standard(s) cULus Listed
Environmental Conditions Indoor and Outdoor

Dimensions

Weight 1.2 lb.

General

Material - Mounting Hardware Type	Stainless Steel Screw Mounting Accessories
Enclosure Type Series	IP69k and UL Type 4X, 12 Non-Fused
Specifications	<ul style="list-style-type: none">• Enclosure Gasket - Neoprene• Handle - Valox®• Shaft (Unfused) - Valox®• Top - Valox®
UPC	783585763309
Ingress Protection Style	IP69k, NEMA Type 4X, 12 Replacement Cover
Color	Gray

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)