

## Locking Devices, Twist-Lock®, Industrial, Male Plug, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2421](#)

Locking Devices, Twist-Lock®, Industrial, Male Plug, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, Black and White



### Features

- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.

### Application

Extra Heavy Duty Industrial

### Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17, Environmental - Moisture Resistance - IP20 Suitability, Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact), Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only., Mechanical - Terminal Identification - Terminals identified in accordance with UL 496

### Specifications

Standards - RoHS Compliance Status	CM
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	L15-20P
Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>

### Conductor

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG
Number Of Poles	3-Pole
Cable Range	0.350 - 1.150 in

### Configuration

Cord Type	All Listed Portables
-----------	----------------------

### Current

Amperage Rating	20 A
Voltage Rating Description	3 Phase 250 VAC
Dielectric Strength	Withstands 2,000V minimum
Current Rating	20 A
Voltage Rating	3 Phase 250 VAC
Connectivity	Pressure Terminal Screws
Phase	Three Phase
Current / Amperage Rating	20 A

### Dimensions

Length	2.33 in
Display Size	Standard Sized
Weight	0.25 lb.
Height	2.75 in
Width	2.33 in
Dimensions	2.33 in x 2.33 in x 2.75 in

### General

Color	Noir, blanc
Cord Range Specifications	0.350"-1.150" (9-29) <ul style="list-style-type: none"> <li>• Assembly Screws - Steel - nickel plated</li> <li>• Blades - Brass</li> <li>• Housing / Cord Clamp - Nylon</li> <li>• Terminal Clamp - Cold rolled steel - nickel plated</li> <li>• Terminal Retainer - Clear polycarbonate</li> <li>• Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)</li> </ul>
UPC	783585038193
Type	Plugs
Material - Mounting Hardware	Cord Mounted
Item Type	20A Male Insulgrip® Plug
Material	Nylon

### Logistics

Pallet Quantity	2400
Carton Quantity	1

## Operational

Operating Temperature

Maximum continuous 75°C and  
minimum -40°C without Impact

Horsepower - Maximum

3

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL2421-SPEC-EN | REV 5/2026