





- 1.) PURCHASED ASSEMBLY -
BLACK PLASTIC HOUSING w/MOLDED HANDLE
40-FT 3-COND 12-GA SJTW CORD
105°C 1875-WATTS 15-AMP 120V 60HZ
w/TRIPLEX RECEPTICLE & RESET BUTTON
& INPUT 24"LG PIGTAIL w3-PRONG PLUG
INCLUDES STEEL MTG BRKT w/PIN and CORD STOP
UNIT IS FOR INDOOR USE ONLY
REEL IS UL LISTED
REEL IS TO HAVE A NAMEPLATE DECAL
(PER GEN.MFG. P/N 9026-5958)
NAMEPLATE TO INCLUDE;
a) THE GLEASON REEL LOGO/NAME
b) THE MODEL NUMBER GR12340-TR
c) CORD DATA & ELECTRICAL RATING INFO
d) THE DATE CODE
e) WARNING INFORMATION
d) THE 'c UL us' LOGO w/CONTROLL No. 528M
- 2.) REEL IS TO HAVE ITS OWN CARTON
THE CARTON SHALL BE PLAIN WITH
MODEL No. GR12340-TR
AND PART No. GR601192
MARKED ON THE EXTERIOR
AN INSTRUCTION SHEET WILL BE INCLUDED
AND PROPER DUNNAGE FOR PROTECTION
- 3.) APPROVED VENDOR -
a, GENERAL MFG., INC
P/N 2200-3022



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE, ECN #57485	2/22/13	JWJ
~	ADD 'GM' P/N f/NAMEPLATE, NO ECN	7/20/13	JWJ
B	'DATE CODE' WAS 'P.O.#', AND	12/10/14	JWJ
"	24" LONG PIGTAIL WAS 36", AND	"	"
"	VNDR #was2200-3000, ECN #58522	"	"
C	CHANGE THE 'c UL us' FILE #, TO BE	3/14/19	JWJ
"	A CONTROLL #, AND CHANGE THE	"	"
"	MTG BRKT TO STEEL, ECN #60601	"	"

RIBBING AND OTHER MISC MINOR DETAILS OMITTED FOR CLARITY
ALL DIMENSIONS ARE REFERENCE FOR GENERAL PART DESCRIPTION

UNLESS OTHERWISE NOTED ALL DIMENSIONS ARE INCHES. TOLERANCES AS FOLLOWS: DECIMAL .X ± .1 DECIMAL .XX ± .03 DECIMAL .XXX ± .010 ANGLES DEG-MIN ± 1°0'	APPLICATION		GLEASON REEL CORPORATION MAYVILLE, WISCONSIN USA
	NEXT ASSY	SIM TO	
THIS DRAWING AND ALL INFORMATION HEREON IS THE PROPERTY OF GLEASON REEL ENG MANUAL. IT MUST NOT BE COPIED, REPRODUCED OR SUBMITTED TO OTHERS WITHOUT WRITTEN AUTHORIZATION AND ALL REPRODUCTIONS ARE SUBJECT TO RETURN ON DEMAND.	DRAWN JWJ	DATE 2/14/13	MEDIUM DUTY CORD REEL 40-ft. 3-cond. 12-ga. SJTW CORD MODEL No. GR12340-TR
	APPROVED	DATE	
	FSCM NO.	DWG NO. 601192	
	DO NOT SCALE THIS DRAWING!	SHEET 1 of 1	