



FRONT




SIDE



BACK

55 °C RISE
SINGLE PHASE 1-10 KVA
INDUSTRIAL CONTROL



BOTTOM

TOTALLY ENCLOSED
ENCAPSULATED DISTRIBUTION TRANSFORMERS

DIMENSIONS										
KVA	A	B	C	D	E	F	G	H	WT. LBS.	TYPE NUMBER
1.00	9.69	12.30	6.78	10.02	7.81	11.29	7.69	7.13	56	T-1-81217
2.00	9.69	13.97	6.78	11.69	7.81	12.96	7.69	7.13	80	T-1-81219
3.00	9.69	13.97	6.78	11.69	7.81	12.96	7.69	7.13	100	T-1-81220
3.00	13.27	14.47	9.75	12.06	11.39	13.46	11.27	11.13	130	T-1-53930
5.00	13.27	14.47	9.75	12.06	11.39	13.46	11.27	11.13	140	T-1-81221
10.00	15.75	16.47	12.94	14.13	13.88	15.46	13.75	14.25	230	T-1-81223

NOTES:

- 1. KNOCKOUTS:
1.69 DIA. FOR 1.25 CONDUIT
1.13 DIA. FOR .75 CONDUIT
.88 DIA. FOR .50 CONDUIT

REVISIONS

- E/ V.A.# 18-500
- F/ ECN 18138
- G/ ECN 18424
- H/ E38-288



OUTLINE

TYPE NO. LUCIFER

DRAWN SJ HUNT/5-9-91 DATE

DESIGN

CHK. JLH APP. MF

MAT'L

FINISH

SCALE NONE SHEET 1 OF 1

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES
TOLERANCE ON:
2 PLACE DECIMALS ± .02
3 PLACE DECIMALS ± .015

DO NOT SCALE DRAWING

CADD DWG 70007045