


- 12 .250 SPLIT LOCK WASHER
- 39 .250-20 HEX NUT
- 40 .250 FLAT WASHER
- 3 BLOWOUT CORE INSULATOR
- 38 STANDOFF SPACER (3)
- 5 BLOWOUT CORE
- 30 .375 FLAT WASHER
- 35 .375 LOCK WASHER
- 37 .375-16 X 1.25 LG. HEX HEAD SCREW
- 34 .312-18 X 1.50 LG. HEX HD. SCREW S.S.
- 31 .312 MED. SPRING LOCK WASHER
- 33 BLOWOUT COIL SPACER
- 9 CONTACT TIP
- 53 .312-18 X .75 LG. HEX HEAD SCREW S.S.
- 31 .312 MED. SPRING LOCK WASHER
- 50 CONTACT SPRING
- 28 HAIR COTTER PIN (2)
- 43 ARMATURE BEARING PIN
- 74 ARMATURE BUSHING
- 24 STATOR ASSEMBLY
- 56 PLUNGER AUXILIARY CONTACT
- 58 #6-32 X 1.00 LG. PAN HEAD SCREW (2)
- 59 #6 INT. TOOTH LOCK WASHER (2)
- 1 BASE ASSEMBLY
- 26 STATOR CORE
- 23 CORE CAP
- 52 CORE CAP SPACER
- 25 .375-16 X 1.00 LG. HEX HD. SCREW
- 17 .375 FLAT WASHER
- 35 .375 LOCK WASHER
- 42 .250-20 X 1.25 LG. HEX HD. SCREW
- 41 ARC SHIELD RETAINER
- 4 BLOWOUT COIL OR BLOWOUT COIL ASSY
- 6 BLOWOUT COIL INSULATING WASHER (2)
- 8 BLOWOUT GUARD
- 7 STATIONARY CONTACT BRACKET
- 55 ARC TRANSFER TIP
- 9 CONTACT TIP
- 32 .312-18 X 1.00 LG. HEX HEAD SCREW S.S.
- 31 .312 SPRING LOCK WASHER
- 54 CONTACT HOLDER ARM
- 11 .250-20 X 1.50 LG. FILLISTER HD. SCREW
- 12 .250 SPLIT LOCK WASHER
- 13 .250-20 HEAVY HEX NUT
- 14 .250 FLAT WASHER
- 18 CONTACT BEARING PIN
- 73 CONTACT BUSHING
- 22 ARMATURE ASSEMBLY
- 61 AUXILIARY CONTACT STRIKER
- 62 #10-32 X 2.00 LG. PAN HD. SCREW
- 63 #10 BRASS FLAT WASHER
- 64 #10 INTERNAL TOOTH LOCK WASHER
- 19 OPERATING SPRING

- 44 L.H. FLUX PLATE ASSEMBLY
- 47 .312-18 X 3.50 LG. HEX HEAD SCREW
- 31 .312 SPLIT LOCK WASHER
- 2 BLOWOUT COIL MTG. BASE
- 51 .312-18 X 2.50 LG. HEX HEAD SCREW (3)
- 20 .312 FLAT WASHER (3)
- 31 .312 SPLIT LOCK WASHER (3)
- 71 SINGLE AUX KIT
- 45 ARC SHIELD ASSEMBLY
- 46 R.H. FLUX PLATE ASSEMBLY
- 29 .312-18 HEX NUT
- 31 .312 SPLIT LOCK WASHER
- 49 .375-16 X 2.25 LG. STUD BRASS
- 36 .375 FLAT WASHER BRASS (3)
- 48 .375-16 HEX NUT BRASS (3)
- 71 DOUBLE AUX KIT
- 15 FINGER SHUNT ASSEMBLY
- 72 SPIROL WRAP
- NOTE: ORDER 8.50 INCH PIECE
- 49 .375-16 X 2.25 LG. STUD BRASS
- 36 .375 FLAT WASHER BRASS (3)
- 48 .375-16 HEX NUT BRASS (3)
- 68 ARC SUPPRESSOR STRAP (2)
- 67 ARC SUPPRESSOR
- 66 #8 INTERNAL TOOTH LOCK WASHER (2)
- 69 #8-32 X .625 LG. FILL. HD. SCREW (2)

☐ APPLY VIBRATITE TO THREADS
 Ⓛ TIGHTENING PROCEDURE: RUN THE HEX NUT UP TO THE SCREW HEAD. TURN THE SCREW UNTIL IT IS TIGHT AGAINST THE PIVOT PIN (APPROX 25 IN-LBS). TIGHTEN NUT DOWN AGAINST THE LOCK WASHER, FLAT WASHER, AND SHUNT.

ALL DIMENSIONS IN INCHES



MODEL 99

THIS DRAWING FILE AND THE DATA SHOWN IS PROPRIETARY AND CONFIDENTIAL AND THE SOLE PROPERTY OF HUBBELL INDUSTRIAL CONTROLS. DO NOT USE OR REPRODUCE WITHOUT WRITTEN APPROVAL OF HUBBELL.

E				LINEAR	HOLE	ANGLES	RENEWAL PARTS BULLETIN 5210 FIBERGLASS BASE 300 AMPERE NORMALLY CLOSED DC CONTACTOR SIZE #5 DB
D				0.X ±.050	PUNCH ±.002	DIMEN. ± 1'	
C				0.OX ±.020	±.50	UNDIM. 90° ±2'	
B	7/27/12	KEG	NEW ARC CHUTE, ECN A12-054	0.OXX ±.005	REAM SPECIFIED	CADD NO. 58900701	
A	1-25-01	TLJ	REMOVED ITEM 16 (NOW ITEM 31)	R.M.S.	DATE 6-28-99	DR.T. JOHNSON [CK.]	REF.
Rev	DATE	BY	DESCRIPTION	Hubbell Industrial Controls, Inc. 50 Edwards Street Madison, Oh. 44057			