



- (FOR 50 AMP CONTACTOR)
- 88 .250-20 X 1.25 BRASS RD HD SCREW
 - 60 .250 BRASS (3) FLAT WASHER
 - 58 .250-20 HEX NUT
 - 61 .250 INTERNAL TOOTH LOCK WASHER
 - 62 #10-32 X 1.25 LG. ROUND HEAD SCREW
 - 64 #10 BRASS FLAT WASHER (4)
 - 69 #10-32 X .37 LG PAN HD SCREW
 - 73 #10-32 HEX NUT (2)
 - 74 #10 INTERNAL TOOTH LOCK WASHER

- 65 #8 SPLIT LOCK WASHER
- 66 #8-32 HEX NUT
- 67 #8-32 X .75 LG. ROUND HEAD SCREW
- 68 #8 FLAT WASHER
- 69 #10-32 X 1.25 LG. ROUND HEAD SCREW
- 70 #10 BRASS FLAT WASHER (2)
- 71 #10-32 X .37 LG PAN HD SCREW
- 72 #10 INTERNAL TOOTH LOCK WASHER
- 73 #10-32 HEX NUT (2)
- 74 #10 INTERNAL TOOTH LOCK WASHER
- 75 #8 SPLIT LOCK WASHER (2)
- 76 #8-32 X 1.50 LG. ROUND HEAD SCREW (2)
- 77 #8 FLAT WASHER (2)
- 78 #10-32 X 1.25 LG. ROUND HEAD SCREW
- 79 #10 BRASS FLAT WASHER (2)
- 80 #10-32 X .37 LG PAN HD SCREW
- 81 #10 INTERNAL TOOTH LOCK WASHER
- 82 #10-32 X 1.25 LG. ROUND HEAD SCREW
- 83 #10 BRASS FLAT WASHER (2)
- 84 #10-32 X .37 LG PAN HD SCREW
- 85 #10-32 X 1.25 LG. ROUND HEAD SCREW
- 86 #10 BRASS FLAT WASHER (2)
- 87 #10-32 HEX NUT (2)
- 88 #10 INTERNAL TOOTH LOCK WASHER

- (FOR 50 AMP CONTACTOR)
- 86 .250-20 X 1.25 LG. ROUND HEAD SCREW
 - 60 .250 FLAT WASHER
 - 58 .250-20 HEX NUT
 - 61 .250 INTERNAL TOOTH LOCK WASHER

NOTE: SEE SHEET 2 FOR MATERIAL LIST

THIS DRAWING FILE AND THE DATA SHOWN IS PROPRIETARY AND CONFIDENTIAL AND THE SOLE PROPERTY OF HUBBELL INDUSTRIAL CONTROLS. DO NOT USE OR REPRODUCE WITHOUT WRITTEN APPROVAL OF HUBBELL.

E				LINEAR	HOLE	ANGLES	
D				O.X ±.050	PUNCH ±.002	DIMEN. ± 1'	
C				O.XX ±.020	±.50	±.002	
B	3/4/13	KEG	ECN A13-019 CHANGE SCREW	O.OXX ±.005	±.50	±.002	
A	7/27/12	KEG	NEW ARC CHUTE, ECN A12-054	CADD NO. 59656003	±.50	±.002	
Rev	DATE	BY	DESCRIPTION	R.M.S.	DATE 12-6-03	DR.LMH	CK. REF.



Hubbell Industrial Controls, Inc.
50 Edwards Street Madison, Oh. 44057

REPAIR PARTS BULL 5110 & 5210
NEMA SIZE 5A, 400 AMP CONTACTOR
MOLDED BASE & FABRICATED ARMATURE
MODEL 2001, WITH NC POWER POLE

DRG. NO 1 OF 2
RPC-59656-2