





NOTE:
PRIMARY AND SECONDARY BUS AREA
IN FRONT OF CASE.

KEY: DENOTES CONDUIT AREAS



Primary Volts	Alt Rating	Connect Primary Lines To	Inter-Connect	Connect Secondary Lines To
600	480	H1, H2, H3	1	
570	456	H1, H2, H3	2	
540	432	H1, H2, H3	3	

Secondary Volts				
480	380			X1, X2, X3
277 1 phase	220 1 phase			X1 to X0 X2 to X0 X3 to X0

Revisions



Type No.

DATE:

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
225	T-2A-52715-1	600 (Auto)	480 (Auto)	WS-A-2	600 Lbs	3 ϕ	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C	Regulation @ 100% PF		Impedance		Typical Efficiency-35%	99.23%
Insulation	220°C					No Load Losses	
Sound Level	55 dB	NEMA Standard		Windings		Total load Losses	
				AL			

A

PRINTS
TO

CONTROL
7

A