


M-12603 3



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BASE	GALV STEEL	WHITE POWDERCOAT
MAIN ENCLOSURE	GALV STEEL	WHITE POWDERCOAT
CIRCUIT HOUSING	GALV STEEL	WHITE POWDERCOAT
POWER CORD	THERMOPLASTIC	WHITE
SCREWS	STEEL	ZINC
HG DUPLEX RECEPTACLE	THERMOPLASTIC	WHITE
OUTLET COVERS	THERMOPLASTIC	
HEX NUTS	STEEL	ZINC
KNURLED NUT	S. STEEL	-
SCREW	S. STEEL	-

3	IN NOTES: VPR WAS 500V, ADDED In RATING. PER DCN# 23185	EMD	6/22/17
2	PRODUCT DESCRIPTIONS UPDATED; EQUIP. GR. TERM. WAS RETURN GR. TERM. .32 WAS .35. ADDED NOTES. DRAWING TITLE REVISED. PER DCN#22739	EMD	11/11/16
1	RELEASED PER DCN# 20544	EMD	6/2/14
SYM	DESCRIPTION	APPROVED	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
HCOA SURGE STRIP

NOTE:
MEETS UL STANDARD 2930
MCOV: 150V, VPR: 600V (L-N), ENERGY RATING: 550J, In= 3kA
ALL MODELS ARE EQUIPPED WITH TAMPER RESISTANT HG RECEPTACLES

CATALOG#	DESCRIPTION	CORD LENGTH	RATING
HBL6MG6	15A UL HCOA SURGE STRIP 6' CORD	6 FT	15A 125V
HBL6MG15	15A UL HCOA SURGE STRIP 15' CORD	15 FT	15A 125V
HBL6MG620	20A UL HCOA SURGE STRIP 6' CORD	6 FT	20A 125V
HBL6MG1520	20A UL HCOA SURGE STRIP 15' CORD	15 FT	20A 125V

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
FRACTIONS ~ 1/64	DR. BY EMD	APP. BY
DECIMALS ~ .005	TR. BY	SCALE
ANGLES ~ 2~	CHK'D BY	DATE 5/28/2014

DIMENSION SHEET FOR CAT. NO. SEE TABLE
 REPAIRABLE
 NON-REPAIRABLE
B
M-12603
3