

YAE18N56FBOX

by Burndy
Catalog ID: YAE18N56FBOX

Prop 65 Notice

Cu Terminal, Fork Tongue, 22-16 AWG; #4-#6 stud, Nylon Insulated, Tin Plated, Multi-Finger Insulation Grip



Product Details

General

Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
Type	Ring Tongue
UPC	781810367575
UPC 12 Digit	7818103675755

Dimensions

Dimension - B Length fraction	5/32 in
Dimension - B Length inch	0.16 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.82 in
Dimension - N inch	0.11 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z inch	0.21 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18;AN 16
Conductor - Copper Str Size Range	20 AWG-16 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)