

YAE18N57FBOX

by Burndy
Catalog ID: YAE18N57FBOX

Prop 65 Notice

Cu Terminal, Fork Tongue, 22-16 AWG; #6-#8 stud, Nylon Insulated, Tin Plated, Multi-Finger Insulation Grip



Product Details

General

Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
Type	Ring Tongue
UPC	781810367582
UPC 12 Digit	7818103675822

Dimensions

Cable Insulation Diameter Maximum	0.125 in
Dimension - B Length fraction	4/25 in
Dimension - B Length inch	0.16 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.96 in
Dimension - N inch	0.18 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	3/16 in
Dimension - Stud Size inch	#6;#8
Dimension - Z inch	0.28 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18;AN 16
Conductor - Copper Str Size	20;18;16
Conductor - Copper Str Size Range	20 AWG-16 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)