



## YAE22N66FM

by Burndy  
Catalog ID: YAE22N66FM

Prop 65 Notice

Cu Terminal, Fork Tongue, 24-20 AWG; #4-#6 stud, Nylon Insulated, Tin Plated, Multi-Finger Insulation Grip, Reel Packaging

## Product Details

### General

Color Code	Amber
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	INSULUG™
UPC	781810028674
UPC 12 Digit	7818100286744

### Dimensions

Dimension - B Length fraction	10/91 in
Dimension - B Length inch	0.11 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.8 in
Dimension - N inch	0.12 in
Dimension - Pad Width inch	0.28 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z inch	0.27 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Aircraft Size	AN 26;AN 22;AN 20
Conductor - Copper Str Size	20 AWG

Conductor - Copper Str Size Range	24 AWG-20 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	2000
Packaging Type	Reel

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)