



## YAEV4CRS2

by Burndy  
Catalog ID: YAEV4CRS2

TERMINAL-NYLON INSULATED-RING-TONGUE, 300 VOLTS MAX. 105° C MAX.

### Product Details

#### General

Color Code	Yellow
Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810039526
UPC 12 Digit	7818100395266

#### Dimensions

Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - D inch	1.33 in
Dimension - G inch	1.02 in
Dimension - Hole Size inch	0.40 in
Dimension - Length Overall inch	1.28 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.50 in
Dimension - Pad Width inch	0.62 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	90 Degree

#### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper Str Aircraft Size Range	AN 4
Conductor - Copper Str Size	4
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL486</li> <li>• Military Specified (Mil-Spec)</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	250
-----------------------	-----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)