



YAEV8CRS1

by Burndy
Catalog ID: YAEV8CRS1

Nylon-Insulated Right-Angle Copper tube Terminals, 8 Max. Insul. Dia.: .258" Sleeve, Color: Red, 1/4, 1.25 in L, .41in W, Tin-Plated, 600 Volts Max.

Nylon-insulated right-angle terminals, made of seamless pure copper tubing

Product Details

General

Application	Designed to Accommodate Larger Conductor Insulation Diameters
Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, INSULUG
Trade Name	INSULUG™
Type	YAEV-RS
UPC	781810039496
UPC 12 Digit	7818100394966

Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.53 in
Dimension - G inch	0.84 in
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	1.25 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.36 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	1/4

Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Aircraft Size Range	AN 6
Conductor - Copper Str Size	8
Conductor - Copper Str Size Range	8
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	500
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)