

CATALOG NUMBERS

AMPERE RATINGS

M1K
M2K
M3K

1
2
3

M6K
M8K
M10K
M12K
M15K
M20K
M25K
M30K
M40K
M50K
M65K
M80K
M100K

6
8
10
12
15
20
25
30
40
50
65
80
100

M140K

140

M200K

200

K
MINIMUM
MELTING
TIME

.8 CYCLE - MINIMUM TIME FOR SAFE COORDINATION


MINIMUM MELTING Time-Current Characteristic Curves

For: CHANCE TYPE "K" (FAST) Fuse Links In Chance Cutouts

Basis for data: ANSI/IEEE Standard C37.41 - 1988

1. Tests made at less than rated cutout voltage starting at 25C with no initial load.
2. Curves are plotted to minimum test points so variations should be plus.

30002



Centralia, MO Rev. A. 3/95