



LUMINAIRE: SAV-LH-40-8-WA16-CDL-U-GG
Savanno Decorative Led, Highbay
16" led with clear acrylic refractor and conical drop lens
Data Scaled from Test# 17.00879

TEST #18257
DATE: 3/29/2017

CANDELA VALUES

| ANGLE | 0.0 |
|-------|--------------|
| 0.0 | 4514 |
| 2.5 | 4541 |
| 5.0 | 4708 |
| 7.5 | 4762 |
| 10.0 | 4725 |
| 12.5 | 4835 |
| 15.0 | 5019 |
| 17.5 | 5124* |
| 20.0 | 5004 |
| 22.5 | 4674 |
| 25.0 | 4472 |
| 27.5 | 4347 |
| 30.0 | 3987 |
| 32.5 | 3462 |
| 35.0 | 2780 |
| 37.5 | 2304 |
| 40.0 | 1849 |
| 42.5 | 1559 |
| 45.0 | 1142 |
| 47.5 | 806 |
| 50.0 | 604 |
| 52.5 | 468 |
| 55.0 | 385 |
| 57.5 | 325 |
| 60.0 | 273 |
| 62.5 | 227 |
| 65.0 | 194 |
| 67.5 | 171 |
| 70.0 | 145 |
| 72.5 | 120 |
| 75.0 | 93 |
| 77.5 | 74 |
| 80.0 | 57 |
| 82.5 | 50 |
| 85.0 | 40 |
| 87.5 | 36 |
| 90.0 | 36 |
| 92.5 | 36 |
| 95.0 | 41 |
| 97.5 | 49 |
| 100.0 | 53 |
| 102.5 | 59 |
| 105.0 | 65 |
| 107.5 | 70 |
| 110.0 | 73 |
| 112.5 | 76 |
| 115.0 | 77 |
| 117.5 | 80 |
| 120.0 | 79 |
| 122.5 | 82 |
| 125.0 | 83 |
| 127.5 | 85 |
| 130.0 | 85 |
| 132.5 | 84 |
| 135.0 | 82 |
| 137.5 | 80 |
| 140.0 | 75 |
| 142.5 | 71 |
| 145.0 | 67 |
| 147.5 | 64 |
| 150.0 | 61 |
| 152.5 | 58 |
| 155.0 | 56 |
| 157.5 | 56 |
| 160.0 | 60 |
| 162.5 | 65 |
| 165.0 | 68 |
| 167.5 | 69 |
| 170.0 | 69 |
| 172.5 | 67 |
| 175.0 | 62 |
| 177.5 | 66 |
| 180.0 | 68 |

*MAXIMUM CANDELA VALUE