





TRANSFORMER SPECIFICATIONS	
PRIMARY VOLTAGE(S)	208/230/460
SECONDARY VOLTAGE(S)	115
RATED V.A.	750
RATED FREQUENCY	50/60
INSULATION CLASS	130°C @ MAX, RISE 80°C
AGENCY APPROVALS	UL, CUL
ESTIMATED WEIGHT	28.1 LBS



SECONDARY SIDE PRIMARY SIDE



CONNECTION DIAGRAM

DIMENSIONS ARE IN INCHES		NAME	DATE
TOLERANCES:		DRAWN BY:	VS 05/07/2020
.XX	± .03	CHECKED BY:	
.XXX	± .010		
ANGULAR:	± 1°		
SOURCE	N/A	PROPRIETARY AND CONFIDENTIAL	
MATERIAL	N/A	THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME IS PROHIBITED.	
FINISH	N/A		
DO NOT SCALE DRAWING			



DESCRIPTION:	
750 VA	
SIZE	DWG. NO.
A	TB750N005F0