



## DYNC Series

- NEMA4X
- UL Sanitation Certified

- Spectron®  
Self-Test/Self-Diagnostics

Part Number	Catalog Number	UPC Code	Description	CA 03	GA 27	IL 06	PA 10	TX 04	Wt. each	Ctn. Qty
93093075	DYNCSRW6	782520869991	Single Face, Red Letters, White Hsg, 6W Capacity, 3W lamps	●	●				14 lbs.	2 ea.
93093076	DYNCDRW6	782520870010	Double Face, Red Letters, White Hsg, 6W Capacity, 3W lamps	●	●				14 lbs.	2 ea.
93093077	DYNCSRW12	782520870034	Single Face, Red Letters, White Housing, 12W Capacity, 3W lamps	●	●				14 lbs.	2 ea.
93093078	DYNCDRW12	782520870058	Double Face, Red Letters, White Housing, 12W Capacity, 3W lamps	●	●				14 lbs.	2 ea.
93093079	DYNCSRW12-06L	782520870072	Single Face, Red Letters, White Housing, 12W Capacity, 6W lamps	●	●				14 lbs.	2 ea.
93093080	DYNCDRW12-06L	782520870089	Double Face, Red Letters, White Housing, 12W Capacity, 6W lamps	●	●				14 lbs.	2 ea.
93093085	DYNCSGW12-06L	782520870171	Single Face, Green Letters, White Housing, 12W Capacity, 6W lamps	●					14 lbs.	2 ea.
93093086	DYNCDGW12-06L	782520870188	Double Face, Green Letters, White Housing, 12W Capacity, 6W lamps	●					14 lbs.	2 ea.
93093089	DYNCSR12	782520870232	Single Face, Red Letters, Black Housing, 12W Capacity, 3W lamps	●	●				14 lbs.	2 ea.
93093090	DYNCDR12	782520870256	Double Face, Red Letters, Black Housing, 12W Capacity, 3W lamps	●	●				14 lbs.	2 ea.