



2L-RW-D*

The MOD™ 2L LED Recessed Wall Direct (2L-RW-D) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



Click RDC/QS Guide for full details.



10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 150

2L	PT						
SERIES	MOUNTING	FIXTURE DISTRIBUTION	WALL LENGTH	CEILING LENGTH	WALL LENGTH ADDER	CEILING LENGTH ADDER	MAX LENGTH IN ROW
2L MOD	PT Drywall with plaster trim (trimless finish)	WDC Direct WCAD Asymmetric Direct	' W Enter in foot increments	' C Enter in foot increments	.3 Wall length +3" .6 Wall length +6" .9 Wall length +9" Measured in Inches	.3 Wall length +3" .6 Wall length +6" .9 Wall length +9" Measured in Inches	02 2', 609mm 03 3', 914mm 04 4', 1219mm 05 5', 1524mm 06 6', 1829mm 08 8', 2438mm

					1C	
DIRECT OPTICAL DISTRIBUTION	FINISH/COLOR ²	COLOR TEMPERATURE	DIRECT OUTPUT/FT ⁶	DRIVER	CIRCUITING	VOLTAGE
SOF Soft Diffuse Lens, Lambertian	C1 Matte White (Default)	27K 2700K ¹ 30K 3000K 35K 3500K 40K 4000K 50K 5000K ¹	D030 300 (min) to D085 850 (max)	D01 1% Dimming, 0-10V D00 1% Dim-to-Off, 0-10V D05 SpectraSync 5% Dimming, 0-10V ¹⁰ DS1 1% Dimming w/ Soft Start, 0-10V DS0 1% Dim-to-Off w/ Soft Start, 0-10V LEC Hi-lume 1% Ecosystem LED Driver DALI DALI ¹ DALIP Powered by DALI (2.0) ¹ NDM Non-Dimming	1C 1 Circuit	UNV Universal Voltage (120V-277V) 347 347 Volt ^{1,7}
ASYM Asymmetric Diffuse Lens ^{3,4}	C2 Textured Matte White C3 Light Silver C4 Machined Aluminum	27K9 2700K, 90 CRI ¹ 30K9 3000K, 90 CRI 35K9 3500K, 90 CRI 40K9 4000K, 90 CRI 50K9 5000K, 90 CRI ¹	2230TD 2200K-3000K SpectraSync™ Dim-to-Warm ⁵ 2750T 2700K-5000K SpectraSync™ Tunable White ⁵ 2765T 2700K-6500K SpectraSync™ Tunable White ⁵			
BAT Batwing Lens	C5 Carbon Black C6 Textured Camera Black					

OPTIONAL

NIGHTLIGHT	EMERGENCY	THRU-WIRING	CHICAGO ENVIRONMENTAL AIR MODIFICATION
NL Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row	EF 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. ⁹	W1 No Thru Wire W2 Provide Normal and Emergency/Nightlight Thru Wiring ¹¹ W3 Provide Normal Thru Wiring Only	CCEA Chicago Environmental Air Modification

Notes:

- Additional lead time may be applicable. Contact factory.
- Visit www.litecontrol.com/finishes for details.
- Not Available with Patterns.
- Must be ordered with IAD.
- Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- Suspension Kit: 3/64" diameter field-adjustable aircraft cable. Ships separately. Suspension required at every row joint. Low profile cable gripper limits visibility while providing maximum horizontal balance adjustment.
- EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- Must be ordered with 2230TD, 2750T or 2765T Option
- Only applicable when specified with Emergency/Nightlight.
- Contact Factory for pattern configurations. Approval drawings required. See page 5.