



2L-W-ID*

The MOD™ 2L LED Wall Indirect/Direct (2L-W-ID) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



Click RDC/QS Guide for full details.



10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 150

| 2L | - | W | - | | - | LPAD | - | | - | | - | | - |
|-----------|----------|--|--|----------------------------|--|---|---|--|---|--|---|--|---|
| SERIES | MOUNTING | FIXTURE DISTRIBUTION | INDIRECT OPTICAL DISTRIBUTION | ROW LENGTH | MAX LENGTH IN ROW | DIRECT OPTICAL DISTRIBUTION | | | | | | | |
| 2L MOD | W Wall | ID Indirect/Direct IAD Indirect/Asymmetric Direct | LPAD Low Peak Angle with Diffuser | ' Enter in foot increments | 02 2', 609mm 03 3', 914mm 04 4', 1219mm 05 5', 1524mm 06 6', 1829mm 08 8', 2438mm | SOF Soft Diffuse Lens, Lambertian REG Regressed Diffuse Lens BWO Blade Baffle with Overlay ASYM Asymmetric Diffuse Lens ^{3,4} DRP Drop Lens | | | | | | | |

| | - | | - | | - | | - | | - | |
|---------------------------------|---|---------------------------------|-------------------------------|---|--|--|---|--|---|--|
| FINISH/COLOR ² | COLOR TEMPERATURE | INDIRECT OUTPUT/FT ⁶ | DIRECT OUTPUT/FT ⁶ | DRIVER | CIRCUITING | | | | | |
| C1 Matte White (Default) | 27K 2700K ¹ | I030 300 (min) | D030 300 (min) | D01 1% Dimming, 0-10V | 1C 1 Circuit | | | | | |
| C2 Textured Matte White | 30K 3000K | to | to | D00 1% Dim-to-Off, 0-10V | 2C 2 Circuit - Uplighting / Downlight | | | | | |
| C3 Light Silver | 35K 3500K | I090 900 (max) | D100 1000 (max) | D05 SpectraSync 5% Dimming, 0-10V ⁹ | | | | | | |
| C4 Machined Aluminum | 40K 4000K | | | DS1 1% Dimming w/ Soft Start, 0-10V | | | | | | |
| C5 Carbon Black | 50K 5000K ¹ | | | DS0 1% Dim-to-Off w/ Soft Start, 0-10V | | | | | | |
| C6 Textured Camera Black | 27K9 2700K, 90 CRI ¹ 30K9 3000K, 90 CRI 35K9 3500K, 90 CRI 40K9 4000K, 90 CRI 50K9 5000K, 90 CRI ¹ | | | LEC Hi-lume 1% Ecosystem LED Driver | | | | | | |
| | 2230TD 2200K-3000K SpectraSync™ Dim-to-Warm ⁵ | | | DALI DALI ¹ | | | | | | |
| | 2750T 2700K-5000K SpectraSync™ Tunable White ⁵ | | | DALIP Powered by DALI (2.0) ¹ | | | | | | |
| | 2765T 2700K-6500K SpectraSync™ Tunable White ⁵ | | | NDM Non-Dimming | | | | | | |

OPTIONAL

| | - | | - | | - | | - | |
|--|---|---|---|---|---|--|---|--|
| VOLTAGE | NIGHTLIGHT | EMERGENCY | THRU-WIRING | DUST COVER | | | | |
| UNV Universal Voltage (120V-277V) 347 347 Volt ^{1,7} | NL Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row | EF 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. ⁸ | W1 No Thru Wire W2 Provide Normal and Emergency/ Nightlight Thru Wiring ¹⁰ W3 Provide Normal Thru Wiring Only | L1 Clear Acrylic Dust Cover Lens | | | | |

Notes:

- 1 Additional lead time may be applicable. Contact factory.
- 2 Visit www.litecontrol.com/finishes for details.
- 3 Not Available with Patterns.
- 4 Must be ordered with AD.
- 5 Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- 6 Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- 7 Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- 8 EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- 9 Must be ordered with 2230TD, 2750T or 2765T Option
- 10 Only applicable when specified with Emergency/Nightlight.
- 11 Contact Factory for pattern configurations. Approval drawings required.