



Click RDC/QS Guide for full details.

3L-R-D*

The MOD™ 3L LED Recessed Direct (3L-R-D) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 150

3L						
SERIES	CEILING TYPE ¹	FIXTURE DISTRIBUTION	ROW LENGTH	ROW LENGTH ADDER	MAX LENGTH IN ROW	DIRECT OPTICAL DISTRIBUTION
3L MOD	DW Drywall PT Drywall with plaster trim (trimless finish) LG 15/16 Grid NG 9/16 Grid SS 9/16 Screw Slot	D Direct AD Asymmetric Direct	' Enter in foot increments	.3 Row length +3" .6 Row length +6" .9 Row length +9" Measured in inches	02 2', 609mm 03 3', 914mm 04 4', 1219mm 05 5', 1524mm 06 6', 1829mm 08 8', 2438mm	SOF Soft Diffuse Lens, Lambertian REG Regressed Diffuse Lens ⁴ BWO Blade Baffle with Overlay ⁴ ASYM Asymmetric Diffuse Lens ^{4,5} BAT Batwing Lens DRP Drop Lens ^{2,4}

				1C	
FINISH/COLOR ³	COLOR TEMPERATURE	DIRECT OUTPUT/FT ⁷	DRIVER	CIRCUITING	VOLTAGE
C1 Matte White (Default) C2 Textured Matte White C3 Light Silver C4 Machined Aluminum C5 Carbon Black C6 Textured Camera Black	27K 2700K ² 30K 3000K 35K 3500K 40K 4000K 50K 5000K ² 27K9 2700K, 90 CRI ² 30K9 3000K, 90 CRI 35K9 3500K, 90 CRI 40K9 4000K, 90 CRI 50K9 5000K, 90 CRI ² 2230TD 2200K-3000K SpectraSync™ Dim-to-Warm ⁶ 2750T 2700K-5000K SpectraSync™ Tunable White ⁶ 2765T 2700K-6500K SpectraSync™ Tunable White ⁶	D030 300 (min) ⁸ to D125 1250 (max)	D01 1% Dimming, 0-10V D00 1% Dim-to-Off, 0-10V D05 SpectraSync 5% Dimming, 0-10V ¹¹ DS1 1% Dimming w/ Soft Start, 0-10V DS0 1% Dim-to-Off w/ Soft Start, 0-10V LEC Hi-Lume 1% Ecosystem LED Driver DALI DALI ² DALIP Powered by DALI (2.0) ² NDM Non-Dimming	1C 1 Circuit	UNV Universal Voltage (120V-277V) 347 347 Volt ^{2,9}

OPTIONAL

NIGHTLIGHT	EMERGENCY	THRU-WIRING	CHICAGO ENVIRONMENTAL AIR MODIFICATION
NL Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row	EF 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. ¹⁰	W1 No Thru Wire W2 Provide Normal and Emergency/Nightlight Thru Wiring ¹² W3 Provide Normal Thru Wiring Only	CCEA Chicago Environmental Air Modification

Notes:

- 1 Ceiling type can not be retrofitted in the field.
- 2 Additional lead time may be applicable. Contact factory.
- 3 Visit www.litecontrol.com/finishes for details.
- 4 Not Available with Patterns.
- 5 Must be ordered with IAD.
- 6 Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- 7 Specifiable in 50 Lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- 8 Not available in 2'
- 9 Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- 10 EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- 11 Must be ordered with 2230TD, 2750T or 2765T Option
- 12 Only applicable when specified with Emergency/Nightlight.