




RDC/QS Guide
REGIONAL DISTRIBUTION CENTER STOCK
AND QUICK SHIP PRODUCT GUIDE
www.litecontrol.com

Click RDC/QS Guide for full details.



4L-W-D*

The MOD™ 4L LED Wall Direct (4L-W-D) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



10-Day Quick Ship Ordering Guide Order Limit Per Fixture Selection: 150

4L	W					
SERIES	MOUNTING	FIXTURE DISTRIBUTION	ROW LENGTH	MAX LENGTH IN ROW	DIRECT OPTICAL DISTRIBUTION	FINISH/COLOR²
4L MOD	W Wall	D Direct AD Asymmetric Direct	—' Enter in foot increments	02 2', 609mm 03 3', 914mm 04 4', 1219mm 05 5', 1524mm 06 6', 1829mm 08 8', 2438mm	SOF Soft Diffuse Lens, Lambertian REG Regressed Diffuse Lens BWO Blade Baffle with Overlay ASYM Asymmetric Diffuse Lens ^{3,4} DRP Drop Lens	C1 Matte White (Default) C2 Textured Matte White C3 Light Silver C4 Machined Aluminum C5 Carbon Black C6 Textured Camera Black

			1C	
COLOR TEMPERATURE	DIRECT OUTPUT/FT⁶	DRIVER	CIRCUITING	VOLTAGE
27K 2700K ¹ 30K 3000K 35K 3500K 40K 4000K 50K 5000K ¹ 27K9 2700K, 90 CRI ¹ 30K9 3000K, 90 CRI 35K9 3500K, 90 CRI 40K9 4000K, 90 CRI 50K9 5000K, 90 CRI ¹ 2230TD 2200K-3000K SpectraSync™ Dim-to-Warm ⁵ 2750T 2700K-5000K SpectraSync™ Tunable White ⁵ 2765T 2700K-6500K SpectraSync™ Tunable White ⁵	D030 300 (min) to D125 1250 (max)	D01 1% Dimming, 0-10V D00 1% Dim-to-Off, 0-10V D05 SpectraSync 5% Dimming, 0-10V ⁹ DS1 1% Dimming w/ Soft Start, 0-10V DS0 1% Dim-to-Off w/ Soft Start, 0-10V LEC Hi-lume 1% Ecosystem LED Driver DALI DALI ¹ DALIP Powered by DALI (2.0) ¹ NDM Non-Dimming	1C 1 Circuit	UNV Universal Voltage (120V-277V) 347 347 Volt ^{1,7}

OPTIONAL

NIGHTLIGHT	EMERGENCY	THRU-WIRING
NL Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row	EF 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. ⁸	W1 No Thru Wire W2 Provide Normal and Emergency/Nightlight Thru Wiring ¹⁰ W3 Provide Normal Thru Wiring Only

Notes:

- 1 Additional lead time may be applicable. Contact factory.
- 2 Visit www.litecontrol.com/finishes for details.
- 3 Not Available with Patterns.
- 4 Must be ordered with AD.
- 5 Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- 6 Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- 7 Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- 8 EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- 9 Must be ordered with 2230TD, 2750T or 2765T Option
- 10 Only applicable when specified with Emergency/Nightlight.
- 11 Contact Factory for pattern configurations. Approval drawings required.