



6L-P-ID*

The MOD™ 6L LED Pendant Indirect/Direct (6L-P-ID) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



Click RDC/QS Guide for full details.



10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 150

6L	P	ID	STD			
SERIES	MOUNTING	FIXTURE DISTRIBUTION	INDIRECT OPTICAL DISTRIBUTION	ROW LENGTH	MAX LENGTH IN ROW	DIRECT OPTICAL DISTRIBUTION
6L MOD	P Pendant	ID Indirect/Direct	STD Standard	' Enter in foot increments	02 2', 609mm 03 3', 914mm 04 4', 1219mm 05 5', 1524mm 06 6', 1829mm 08 8', 2438mm	SOF Soft Diffuse Lens, Lambertian REG Regressed Diffuse Lens ³ BWO Blade Baffle with Overlay ³ BAT Batwing Lens

FINISH/COLOR ²	COLOR TEMPERATURE	INDIRECT OUTPUT/FT ⁶	DIRECT OUTPUT/FT ⁶	DRIVER	CIRCUITING
C1 Matte White (Default) C2 Textured Matte White C3 Light Silver C4 Machined Aluminum C5 Carbon Black C6 Textured Camera Black	27K 2700K ¹ 30K 3000K 35K 3500K 40K 4000K 50K 5000K ¹ 27K9 2700K, 90 CRI ¹ 30K9 3000K, 90 CRI 35K9 3500K, 90 CRI 40K9 4000K, 90 CRI 50K9 5000K, 90 CRI ¹ 2230TD 2200K-3000K SpectraSync™ Dim-to-Warm ⁵ 2750T 2700K-5000K SpectraSync™ Tunable White ⁵ 2765T 2700K-6500K SpectraSync™ Tunable White ⁵	I030 300 (min) ⁷ to I135 1350 (max)	D030 300 (min) ⁷ to D125 1250 (max)	D01 1% Dimming, 0-10V D00 1% Dim-to-Off, 0-10V D05 SpectraSync 5% Dimming, 0-10V ¹¹ DS1 1% Dimming w/ Soft Start, 0-10V DS0 1% Dim-to-Off w/ Soft Start, 0-10V LEC Hi-lume 1% Ecosystem LED Driver DALI DALI ¹ DALIP Powered by DALI (2.0) ¹ NDM Non-Dimming	1C 1 Circuit 2C 2 Circuit - Uplighting / Downlight

OPTIONAL

VOLTAGE	SUSPENSION KIT ⁹	NIGHTLIGHT	EMERGENCY	THRU-WIRING	DUST COVER	T-BAR CLIPS
UNV Universal Voltage (120V-277V) 347 347 Volt ^{1,8}	FA1 Suspension Kit, 51" FA2 Suspension Kit, 87" FA3 Suspension Kit, 219" FA4 Suspension Kit, 363"	NL Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row	EF 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. ¹⁰	W1 No Thru Wire W2 Provide Normal and Emergency/Nightlight Thru Wiring ¹² W3 Provide Normal Thru Wiring Only	L1 Clear Acrylic Dust Cover Lens	CB1 T-bar clip - 15/16" CB2 T-bar clip - 9/16" CB3 T-bar clip - 9/16" SS

Notes:

- 1 Additional lead time may be applicable. Contact factory.
- 2 Visit www.litecontrol.com/finishes for details.
- 3 Not Available with Patterns.
- 4 Must be ordered with IAD.
- 5 Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- 6 Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- 7 Not available in 2'
- 8 Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- 9 Suspension Kit: 3/64" diameter field-adjustable aircraft cable. Ships separately. Suspension required at every row joint. Low profile cable gripper limits visibility while providing maximum horizontal balance adjustment.
- 10 EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others. Available in 4'+ fixtures.
- 11 Must be ordered with 2230TD, 2750T or 2765T Option
- 12 Only applicable when specified with Emergency/Nightlight.