



JT8 - Lensed Troffers

- Flush Steel Doors
- Integral T-Bar Clips
- Optimized for T8 Lamps



5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 200

JT8				G	FS			
MODEL	NO. OF LAMPS	CEILING TYPE		SHIELDING		VOLTAGE		OPTIONS
JT8 Dedicated T8 Lensed Troffer	2 Two 3 Three 4 Four (2x4 only)	G Grid		A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal		U 120V-277V		F835 35K 78+CRI Full Wattage T8 Lamps Installed F841 41K 78+CRI Full Wattage T8 Lamps Installed
SIZE	LAMP TYPE	DOOR		BALLAST				
22 2' x 2' 24 2' x 4'	17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2 lamps)	FS White Flush Steel		E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start				
				EL Emergency Battery Pack ² C388 3-Wire Flex C488 4-Wire Flex				

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.