

# LCV- Curv LED



## 10-Day Quick Ship Ordering Guide

Order Limit 1000' Linear Feet (See Alera Express Brochure for Limitations and Details.)

MODEL	LED COLOR	LUMEN PACKAGE	HOUSING TYPE	SUSPENSION LENGTH	VOLTAGE	FINISH	OPTIONS
LCV Curv LED	30 3000K 35 3500K 40 4000K	VW Very Low Watt LW Low Watt ML Medium Lumen HL High Lumen VL Very High Lumen	PERF Perforated S Solid SQP 2" Square Perforated	48 48" 96 96" Other lengths available on request	U 120V-277V	MW Matte White (Std.)	DC Dust Cover <sup>2</sup> SCE Sculpted End Cap (5 <sup>9</sup> / <sub>16</sub> " <sup>2</sup> ) BN Bull Nose End Cap (5 <sup>1</sup> / <sub>16</sub> " <sup>2</sup> ) ELL10 Emergency Battery Pack Installed <sup>3</sup> EMC One Emergency Circuit <sup>1</sup> GTD Generator Transfer Device <sup>1-3</sup> NLC Night Light Circuit <sup>1</sup> GLR Fast Blow Fuse TBAR TBAR Mounting SLC Sloped Ceiling Coupler (45° swivel from vertical) A/B A/B Circuitry
<b>ROW LENGTH</b>		<b>MOUNTING METHOD</b>		<b>DRIVER</b>			
4 4' Single 8 8' Single 12 12' Single — Indicate row length over 12' in 4' increments		CM Adjustable Aircraft Cable Mount		E Fixed Output ED 0-10V Dimming			

**Note:** Rows over 8' will be configured by Alera. Example: 16' will be (2) 8'. Alternate configurations: contact factory.

Specifications apply. Please see Alera Express Program Rules page.

<sup>1</sup> Additional feed drop per EMC, NLC or GTD. (For through wiring, contact factory.)

<sup>2</sup> Ships separately.

<sup>3</sup> For additional, specify quantity before nomenclature (Example: 2ELL10).